

LVT Moisture XT with Acousti-Loc Technology

Milliken

ADHESIVE

For LVT

2.5 mm & 5 mm FLEXFORM™ LVT



pH

NO LIMIT

RH

NO LIMIT



DRY TIME
10 min (wet set)



WORKING TIME
45 mins



CURE TIME
6 hrs



LIGHT TRAFFIC
3 hrs



HEAVY TRAFFIC
4 hrs



HEAVY ROLLING
LOADS : 8 hrs



2-Gallon Pail
Trowel

Unlimited Moisture Vapor Barrier Adhesive

For use with RH up to **No RH Limit**

NO pH or RH LIMITS.
NO TESTING REQUIRED.
NO VAPOR RETARDER REQUIRED

Installation after new pour: **45 days**

NO TESTING REQUIRED.



The Benefits of
Milliken Adhesives

Milliken offers adhesive solutions for any scenario:

- Modular carpet, LVT, mixed-media
- Normal RH and pH
- Extreme RH and no-testing solutions
- Trowel-on and Spray options for most applications
- No primers, no sealants, limited floor prep required

1/16" x 1/32"
x 1/32"
U-Notch

FLOORING TYPE

2.5 mm & 5 mm
FLEXFORM™ LVT

ESTIMATED COVERAGE
150 - 180 sf/gal



IIC
68

Acousti-Loc Technology
provides measurable
acoustic benefits

LVT Moisture XT with Acousti-Loc Technology



PRODUCT CHARACTERISTICS	Product Classification	Modified urethane (isocyanate free)
	Base Chemistry	STPE polymer-based (Hybrid Propel®)
	Curing Method	Moisture cure
	Appearance	Off white
	Consistency	Smooth, low viscosity liquid
	Application	Easy troweling
	Flammability	Non-flammable
	Freeze/Thaw	Stable to 10°F (-12°C)
	Shelf Life	1 year
MOISTURE	Moisture Control	Protects flooring against unlimited moisture
	RH [ASTM F2170]	No testing required (100%)
	pH	No testing required (5-14)
	MVER [ASTM F1869]	No testing required
TIME	Open Time	0 min (Sheet goods/stairs); 10 min (Tile products)
	Dry Time	N/A
	Working Time	45 mins
	Cure Time	6 hours
	Pot Life	N/A
TRAFFIC	Light Traffic	3 hrs
	Heavy Traffic	4 hrs
	Heavy Rolling Loads	8 hrs
SUSTAINABILITY	Solvents	None
	Isocyanates	None
	VOC (g/L) - SCAQMD Rule#1168	0.1
	LEED Points	Contributes to low emitting materials
	Certifications	Greenguard, FloorScore, CRI Green Label Plus
ACOUSTICS	IIC (measured on 6" slab with drop ceiling)	68

STORAGE This product should be stored at temperatures between 50-90°F (15-32° C). While this product is freeze-thaw stable, it is necessary to protect it from freezing. Freeze/thaw stable to 10°F (-12°C).

CAUTION DO NOT take internally. If swallowed, DO NOT induce vomiting. Call a physician immediately. KEEP OUT OF REACH OF CHILDREN.

WARRANTY For Milliken installation instructions and warranties, visit millikenfloors.com.

